












**70585427-00 Timing Belt\_ OEM Screen 4XXX**



70585427-00 Timing Belt\_ OEM Screen 4XXX (Agfa Acento, Heidelberg Topsetter, Fuji Luxel T-XXXX). !!! [\[Timing Belt\\_ OEM Screen 4XXX\]](#)

**86401723 VACUUM PUMP. OEM Screen**



86401723 VACUUM PUMP. OEM Screen (Agfa Acento, Topsetter 74, PT-R 4xxx, Fuji Luxel T-6000) [\[Vacuum Pump OEM Screen\]](#)


**Screen FT-R Interface Cable. OEM Screen**



Screen FT\_R Interface Cable. OEM Screen [\[Screen FT-R Interface Cable\]](#)



Screen Interface Board \_ scsi



Đ°Đ½Ñ,ĐµÑ€Ñ,ĐµĐ¹Ñ•Đ½Đ°Ñ• Đ°Đ°Ñ€Ñ,Đ° Ñ• Đ°Đ°Đ±ĐµĐ»ĐµĐ¼ Đ´Đ»Ñ•  
Ñ,Đ¾Ñ,Đ¾Đ½Đ°Đ±Đ¾Ñ€Đ² Screen FT-R. [\[ĐŸĐ¾Đ´Ñ€Đ±Đ½ĐµĐµ...\]](#)

Đ´Đ»Đ¾Đ° ĐŸĐ,Ñ,Đ°Đ½Đ,Ñ• Cosel PAA300F-5



5 Đ´Đ¾Đ»Ñ€Ñ, 60 Đ•Đ¼Đ¿ĐµÑ€. [\[ĐŸĐ¾Đ´Ñ€Đ±Đ½ĐµĐµ...\]](#)

ĐŸĐ»Đ°Ñ•Ñ,Đ,Đ°Đ¾Đ²Ñ,Đ¹ Đ°ÑfĐ»Đ°Ñ±Đ¾Đ° Đ´Đ»Ñ• Đ•Đ°Đ¼Đ°Đ° Đ´Đ²ĐµÑ€Đ, Đ²  
CTP Screen



Đ´ Đ½ĐµĐ°Đ¾Ñ,Đ¾Ñ€Ñ... Đ¼Đ¾Đ´ĐµĐ»Ñ•Ñ... CTP Screen, Đ²  
Đ¼ĐµÑ...Đ°Đ½Đ,Đ•Đ¼Đµ Đ•Đ°Đ¼Đ°Đ° Đ²ĐµÑ€Ñ...Đ½ĐµĐ¹ Đ´Đ²ĐµÑ€Đ,  
(Đ¿Đ¾Đ´Đ°Ñ±Đ° Đ¿Đ»Đ°Ñ•Ñ,Đ,Đ½) Đ,Đ½Đ¾Đ³Đ´Đ° Đ¼Đ¾Đ¶ĐµÑ,  
Đ²Ñ•Ñ...Đ¾Đ´Đ,Ñ,Ñ€Đ,Đ. Ñ•Ñ,Ñ€Đ¾Ñ• Đ°ÑfĐ»Đ°Ñ±ĐµĐ°-Ñ,Đ¾Đ»Đ°Đ°Ñ,ĐµĐ»Ñ€.  
Đ´Đ°Ñ´ĐµĐ¼Ñf Đ²Đ½Đ,Đ¼Đ°Đ½Đ,ÑŹ Đ¿Ñ€ĐµĐ´Đ»Đ°Đ³Đ°ĐµÑ,Ñ•Ñ•  
Đ•Đ°Đ¿Ñ±Đ°Ñ•Ñ,Ñ€Đ¾Ñ,ĐµÑ±ĐµÑ•Ñ,Đ²ĐµĐ½Đ½Đ¾Đ³Đ¾  
Đ¿Ñ€Đ¾Đ,Đ•Đ²Đ¾Đ´Ñ•Ñ,Đ²Đ°. \*Đ•Ñ•Ñ,Ñ€Đ² Đ½Đ°Đ»Đ,Ñ±Đ,Đ, Đ, Đ´Ñ€ÑfĐ³Đ,Đµ  
Đ•Đ°Đ¿Ñ±Đ°Ñ•Ñ,Đ, Đ,Đ. Đ¿Ñ€Đ¾Ñ±Đ½Đ¾Đ³Đ¾ Đ¿Đ»Đ°Ñ•Ñ,Đ,Đ°Đ°.  
[\[ĐŸĐ¾Đ´Ñ€Đ±Đ½ĐµĐµ...\]](#)







- 
- 
- 
- 
- 

« « Đ' Đ<sup>1/2</sup>Đ°Ñ†Đ°Đ»Đ<sup>3/4</sup>  
« ĐŸÑ€ĐμĐ'Ñ‹Đ'ÑfÑ%Đ°Ñ•  
1  
Đ;Đ»ĐμĐ'ÑfÑŽÑ%Đ°Ñ• »  
Đ' Đ°Đ<sup>3/4</sup>Đ<sup>1/2</sup>ĐμÑ† » »

Đ ĐμĐ.ÑfĐ»ÑœÑ,Đ°Ñ,Ñ‹ 1 - 17 Đ,Đ. 17